

Product Name : " De-Humidifier "
Product Code : " SI 29 "



Description :

De-Humidifier:-

(Fitted with time controlled safety device in, case humidity controller fails, for safety of the compressor). These are water condensing type, based on Refrigeration Cycle to avoid use of expensive chemicals required for desiccant type models. The unit is self- standing and is mounted on a sturdy angle iron frame. Fitted with castor wheels. It removes excess moisture from the atmosphere and is fitted with hermetically sealed compressor. Heat exchanger and water condensing coils are made of copper. Water collection tank is provided below the unit to collect condensate water. Humidity is controlled by HUMIDITY CONTROLLER incorporated in the unit, up to 30% \pm 30% RH, depending upon the ambient conditions. To achieve very low humidity, the room should have an independent window type air conditioner to match with the dehumidifier heat load in the room. Suitable to work on 220/230volts A.C. supply.

Optional (Extra Cost):- Automatic Voltage Stabilizer 4.0 KVA

