

**Product Name :** "-80 Deep Freezer "  
**Product Code :** " SI 44 "



**Description :**

**-80 Degree Deep Freezer :-**

Double wall construction. Inner chamber made of stainless steel sheet. Exterior made out of thick mild steel sheet / Stainless Steel duly finished in white stoving enamel/powder coated paint with finished Colour combinations. Outer double wall door is provided. Temperature working Ambient 30 Degree to -80 Degree. A control panel is provide with various indicators, on-off switch. Digital Temperature Control . Supplied with cord and plug etc. To work on 220VAC Hz single phase.

Inner Chamber Size in mm	Capacity (Approx.)
a) 505x415x830	150 Ltrs.
b) 650x580x900	300 Ltrs.

**Complete With:-**

- i) Digital Temp Indicator cum controller
- ii) Manual Volt meter & On- Off Switch
- iii) Automatic Voltage Stabilizer (**Optional** Extra cost)

