



Product Name : " Automatic Chapatti Making Machine "
Product Code : " CKE 50 "



Description :

Automatic Chapatti Making Machine:-

Roller peda type, L shape:-

Stainless Sheet or mild steel powder coated body on mild Steel angle iron frame. Stainless steel sheeter rollers and hard chrome final rollers. Stainless steel hopper and Teflon coated conveyor. Baking oven is 3 tier are insulated. RV burners for baking and round burners below the wire mesh for puffing. Weight and thickness of the chapatti can be adjusted. Size of chapatti 6",

Capacity 1000 Chapattis Per Hour:-

Consumption of LPG is 3 kgs Per Hour, Power required 2 K.W, Average chapatti size 4 to 6 inch, required perra weight 30 to 50 Grams& minimum space required 20 ft x 20 ft.

Capacity 2000 Chapattis Per Hour:-

Consumption of LPG is 4.5kgs Per Hour, Power required 2 K.W, Average chapatti size 4 to 6 inch, required perra weight 30 to 50 Grams& minimum space required 20 ft x 20 ft.

Capacity 3000 Chapattis Per Hour:-

Consumption of LPG is 7 kgs Per Hour, Power required 3 K.W, Average chapatti size 4 to 6 inch, required perra weight 30 to 50 Grams& minimum space required 20 ft x 20 ft.

Capacity

1000 Chapattis Per Hour
Capacity 2000 Chapattis Per Hour
Capacity 3000 Chapattis Per Hour