

Product Name : " Vacuum Oven "
Product Code : " SI 23 "



chhabrainstruments.com

Description :

Vacuum Oven:-

Double Walled construction, Inner round chamber made out of stainless steel, exterior made our of mild steel duly finished in white stoving enamel/powder coated paint with mat finished colour combinations. Temperature range 50° C to 130°C. The body capable of withstanding vacuum of 760mm hg. Workable on 220VAC 50 Hz single phase. Supplied without vacuum pump.

Chamber size in mm	Capacity(Approx.)
a) 250 x 300 mm	12 Ltrs.
b) 300 x 300 mm	17 Ltrs.
c) 300 x 500 mm	40 Ltrs.

OPTIONAL:-

- i). Digital Temp. Indicator-cum-controller.
- ii). Microprocessor PID digital temp. Indicator-cum-controller.
- iii). Digital Temp. Indicator.

